# GIRA Data sheet



© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

www.gira.com

**System 3000 blind timer and timer Display System 55**




| Specification | Order No. | Packing unit | PS | EAN |
|---|---|---|---|---|
|  cream white glossy | 5366 01 | 1/5 | | 4010337027430 |
|  pure white glossy | 5366 03 | 1/5 | | 4010337027447 |
|  pure white matt | 5366 27 | 1/5 | | 4010337027461 |
|  anthracite | 5366 28 | 1/5 | | 4010337027478 |
|  colour aluminium (lacquered) | 5366 26 | 1/5 | | 4010337027454 |
|  black matt (lacquered) | 5366 005 | 1/5 | | 4010337037484 |
|  grey matt (lacquered) | 5366 015 | 1/5 | | 4010337087243 |
|  stainless steel (lacquered) | 5366 600 | 1/5 | | 4010337027485 |

Illustrations are similar and may deviate from originals.

© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved



**Features**

- Operation via capacitive sensor surface.
- Fast programming for adopting the current time as the programmed movement time/switching time.
- Automatic summer/winter time switchover, deactivatable.
- Switching at sunrise or sunset (astro function) adjustable for 18 countries.
- Astro time for sunrise and sunset can be individually adjusted by ±2 hours.
- The blocking function blocks operation of the auxiliary unit and deactivates automatic mode.
- The display turns off after 2 minutes, permanent display of time is possible.
- Programming one raising and one lowering time or two switch-on and switch-off times for weekdays (Mon-Fri) and for the weekend (Sat+ Sun).

---

**Technical data**

| | |
|---|---|
| Accuracy | |
| - Per month: | ±10 s |
| Power reserve: | approx. 4 h |
| Ambient temperature: | -5°C to +45°C |

---