

Rocker, 2-gang blank System 70



Specification	Order No.	Packing unit	PS	EAN
 pure white glossy	5370 70	1/5		4010337127239
 pure white matt (lacquered)	5370 72	1/5		4010337127246
 anthracite (lacquered)	5370 73	1/5		4010337127291
 black matt (lacquered)	5370 74	1/5		4010337127253
 grey matt (lacquered)	5370 76	1/5		4010337127307

Features

- Button for operating the Gira One system.
- Integrated temperature sensor for measuring the room temperature.
- Programming and start-up with the Gira Project Assistant (GPA), from version 5.0.
- Encrypted data transfer between the Gira One devices.

Operating functions

- Switching of devices, such as lights, socket outlets or pumps.
- Dimming of lights.
- Operation of shading and ventilation devices (blinds, shutters, skylights, roof domes and awnings).
- Convenient group control of switching, dimming, shading and ventilation devices.
- Calling up of scene variants.
- Use as a staircase button to activate the staircase function for switching and dimming devices.
- Floor-call button when combined with the Gira G1.
- Control of Sonos audio devices.
- Controls Hue devices.
- Control of eNet devices
- Door or garage door opener function.
- Boost function.

Illustrations are similar and may deviate from originals.

Room temperature

- Temperature adjustment for the integrated temperature sensor.

LED display

- Brightness value of the status LED can be set to 5 different levels, as well as off.
- Colour of the status LED (red, green, blue) can be set.
- Status LED function can be set depending on the rocker function: always OFF, always ON, actuation display or status display.
- Universally usable for either left or right rocker.

Technical data

Gira One Medium:	Twisted pair (TP), YCYM 2 x 2 x 0.8
Test voltage:	4 kV (KNX/EIB bus line)
Connection:	Connection and junction terminal
Protection class:	III
Installation depth:	15 mm
Ambient temperature:	-5 °C to +50 °C
Current consumption:	8 - 12 mA

Notes

- Can be updated via the Gira Project Assistant (GPA)
 - The rockers are optionally interchangeable with alternative versions.
-