

System 3000 motion detector top unit 1.10 m Standard with DT System 70



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	5379 70	1/5		4010337124917
 pure white matt (lacquered)	5379 72	1/5		4010337124924
 anthracite (lacquered)	5379 73	1/5		4010337124931
 black matt (lacquered)	5379 74	1/5		4010337124948
 grey matt (lacquered)	5379 76	1/5		4010337124955

Merkmale

- Automatic switching of lighting, depending on the movement of heat and ambient brightness.
- Operation with System 3000 switching or dimming insert or 3-wire auxiliary insert.
- Expansion of the detection range in combination with the 3-wire auxiliary insert.
- Adjustable delay time
- Adjustable brightness threshold.
- Sensitivity fixed at 75%.
- If a System 3000 auxiliary insert with operating top unit or mechanical button is connected to the main unit, the lighting can be switched on or dimmed for the duration of the delay time.

With System 3000 dimming insert

- Switch on with the last brightness set, or a saved switch-on brightness.
- The switch-on brightness can only be saved permanently via the System 3000 auxiliary insert with operating top unit.

Technische Daten

Angle of detection:	180°
Delay time - adjustable:	10 s to 30 min
Brightness value - adjustable: - fixed:	approx. 5 to 500 lx Day mode
Sensitivity - permanently set to:	75%
Protection class - System 55, Gira F100: - TX_44:	IP20 IP44
Mounting height up to 1.10 m - Range of detection forwards: - Range to each side:	Max. 32 m Max. 19 m
Ambient temperature:	-20 °C to +45 °C

Hinweise

- The detection field has a horizontal alignment and may not find a limit when used outdoors. For this reason, ensure that the installation location is suitable for outdoor use or use the 2.20 m motion detector top unit.
-

Lieferumfang

- Clip-on panel to limit the detection range is included with delivery.
-