© Copyright by
Gira Giersiepen GmbH & Co. KG
All rights reserved

eNet universal wireless transmitter, 2-gang Mini



Specification	Order No.	Packing unit	PS	EAN
	5453 00	1/5		4010337774310

Features

- The eNet wireless transmitters send switching, dimming and blind motion commands to corresponding eNet wireless receivers.
- The eNet universal wireless transmitter enables the transmission of switching, dimming or blind commands to suitable eNet wireless receivers.
- Mounting in device box, surface-mounted housing or in installation adapter.
- Detection of voltage levels and changes at input.
- Connection of an external status LED.
- Indication of transmission status.
- Operating modes: 1-gang switching/dimming/blind, 1-gang automatic function, 2-gang switching/dimming/button operation, 2-gang automatic function.

Technical data

Ambient temperature:	-5 °C to +45 °C
Wireless frequency:	868.3 MHz
Range (free field):	approx. 100 m
Rated voltage:	AC 110 V to 230 V, 50/60 Hz
Standby:	0.5 W
Inputs	
- Cable length:	Max. 100 m
- Input current:	2 mA
- Signal duration:	min. 200 ms
Output status LED	
- Rated voltage:	AC 110 V to 230 V
- Output current:	40 mA
Dimensions:	Ø 53,0 H 23,0 mm

Illustrations are similar and may deviate from originals.