









## eNet wireless operating top unit arrow symbols



| Spezifikation   | Bestell-Nr. | VE  | PS | EAN           |
|---|-------------|-----|----|---------------|
|  cream white glossy  | 5494 01     | 1/5 |    | 4010337104667 |
|  pure white glossy | 5494 03     | 1/5 |    | 4010337104650 |
|  pure white matt   | 5494 27     | 1/5 |    | 4010337104643 |
|  anthracite        | 5494 28     | 1/5 |    | 4010337104636 |
|  colour aluminium  | 5494 26     | 1/5 |    | 4010337104629 |
|  black matt        | 5494 005    | 1/5 |    | 4010337104605 |
|  grey matt         | 5494 015    | 1/5 |    | 4010337104599 |
|  stainless steel   | 5494 600    | 1/5 |    | 4010337104612 |

## Merkmale

- Operation on switching, dimming or blind insert or 3-wire auxiliary insert from System 3000.
- Manual, wireless and time-controlled operation of e.g. blinds, shutters, awnings, lighting or fans.
- Transmitter for wireless transmission of switching, dimming and blind commands.
- Adjustable night mode. Status LED and function LED are not lit up continuously.
- Status feedback to wireless transmitter.
- Status display with LED.
- Evaluation of auxiliary inputs.

Functions in combination with blind insert:

- Positioning of hangings via scene call-up.
- Position for sun protection and twilight.
- Runtime and ventilation position of the curtain can be saved.

Functions in combination with light insert:

- Scene operation possible.
- Switch-on brightness can be permanently stored when combined with dimming insert.

Functions in combination with 3-wire auxiliary unit:

- Power-supplied eNet transmitter.
- Lighting control.
- Shading control.

Adjustable with eNet server version 2.3 and higher (depending on the insert):

- Fully encrypted wireless transmission (AES-CCM).
- Deactivate auxiliary unit evaluation.
- Operation locks.
- Reversal time adjustable for blinds, shutters and awnings.
- Direction of travel can be inverted.
- Position for sun protection, twilight, lock-out protection and wind alarm.
- Maximum brightness, minimum brightness and dimming speed adjustable.
- Function of the status LED can be set as status LED/actuation display.
- Delay time.
- Switch-on/off delay.
- Dimming ramp up/down.
- Switch-off pre-warning.
- Permanent-on, permanent-off.
- Hotel function.
- Light control.
- Repeater function.
- Device software update.

---

## Technische Daten

|                      |                    |
|----------------------|--------------------|
| Ambient temperature: | -5 °C to +45 °C    |
| Wireless frequency:  | 868.0 to 868.6 MHz |
| Range (free field):  | approx. 100 m      |

---

## Hinweise

- Using a metal cover frame can lead to impairments to the range
  - Radio approval is valid for EU and EFTA countries.
-