



USB 3.0 type A insert, 2-gang Breakout cable



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	5685 03	1		4010337462095
 black matt	5685 10	1		4010337462101

Technische Daten

Installation depth	
- Breakout cable:	mind. 46 mm
Length of the breakout cable:	200 mm

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.: 1068-02
Cavity mounting: Kaiser order no.: 9062-94
Concrete installation: Kaiser order no.: 1268-40