

Modular Jack RJ45 cat.6A 10 Gbit Ethernet insert and SAT F jack Gender changer, SAT F, insulation displacement connector, modular jack



Spezifikation	Bestell-Nr.	VE	PS	EAN
 pure white glossy	5697 03	1/5		4010337463399
 black matt	5697 10	1/5		4010337463405

Technische Daten

Installation depth:	35 mm
Wave impedance for SAT:	75 Ω
For internal conductors:	Ø 0.6 to 1 mm

Hinweise

- For screw attachment only.
- Important! Observe construction space for plug and bending radii.
- When these plug-and-socket devices are used, there is a power limit of 15 watts for connected devices.
- If using with couplers: Not suitable for trunking installation and standard device box. Connection with angled plug recommended.
- Recommended installation: Kaiser electronic boxes
Flush-mounted installation: Kaiser order no.: 1068-02
Cavity mounting: Kaiser order no.: 9062-94
Concrete installation: Kaiser order no.: 1268-40