







Marco cobertor Gira F100 antracita (pintado)



Especificación	Ref.	UE	SP	EAN
 1 elemento	0211 173	1/10		4010337135951
 2 elementos	0212 173	1/10		4010337133568
 2 elementos sin listón central	1002 173	1/10		4010337133605
 3 elementos	0213 173	1/5		4010337133575
 4 elementos	0214 173	1/5		4010337133582
 5 elementos	0215 173	1/5		4010337133599

Características

- En el color blanco puro brillante: fabricado con un 85 % de plástico biocircular.

Datos técnicos

Marco cobertor 1e:	B 83,3 x H 83,3 x T 10,6
Marco cobertor 2e:	B 83,3 x H 154,4 x T 10,6
Marco cobertor 2e s/LC:	B 83,3 x H 154,4 x T 10,6

Marco cobertor 3e:	B 83,3 x H 225,9 x T 10,6
Marco cobertor 4e:	B 83,3 x H 297,2 x T 10,6
Marco cobertor 5e:	B 83,3 x H 368,5 x T 10,6
Radio de esquina:	R 3
Plastica biocircolare - Color: blanco brillante:	mín. 50 %
