







## Marco cobertor Gira F200 blanco brillante



| Especificación   | Ref.    | UE   | SP | EAN           |
|--|---------|------|----|---------------|
|  1 elemento                       | 0211 70 | 1/10 |    | 4010337113171 |
|  2 elementos                    | 0212 70 | 1/10 |    | 4010337113225 |
|  2 elementos sin listón central | 1002 70 | 1/10 |    | 4010337113430 |
|  3 elementos                    | 0213 70 | 1/5  |    | 4010337113270 |
|  4 elementos                    | 0214 70 | 1/5  |    | 4010337113331 |
|  5 elementos                    | 0215 70 | 1/5  |    | 4010337113386 |

### Características

- En el color blanco puro brillante: fabricado con un 85 % de plástico biocircular.

### Datos técnicos

|                         |                           |
|-------------------------|---------------------------|
| Marco cobertor 1e:      | B 90,0 x H 90,0 x T 11,4  |
| Marco cobertor 2e:      | B 90,0 x H 161,1 x T 11,4 |
| Marco cobertor 2e s/LC: | B 90,0 x H 161,1 x T 11,4 |

|   |                           |
|---|---------------------------|
| Marco cobertor 3e:                                  | B 90,0 x H 232,6 x T 11,4 |
| Marco cobertor 4e:                                  | B 90,0 x H 303,9 x T 11,4 |
| Marco cobertor 5e:                                  | B 90,0 x H 375,2 x T 11,4 |
| Radio de esquina:                                   | R 0,3                     |
| Plastica biocircolare<br>- Color: blanco brillante: | mín. 50 %                 |

---