

## Marco cobertor Gira F300 blanco brillante



| Especificación                                                                                                     | Ref.    | UE   | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------------|---------|------|----|---------------|
|  1 elemento                       | 0211 80 | 1/10 |    | 4010337113478 |
|  2 elementos                    | 0212 80 | 1/10 |    | 4010337113539 |
|  2 elementos sin listón central | 1002 80 | 1/10 |    | 4010337131830 |
|  3 elementos                    | 0213 80 | 1/5  |    | 4010337113584 |
|  4 elementos                    | 0214 80 | 1/5  |    | 4010337113638 |
|  5 elementos                    | 0215 80 | 1/5  |    | 4010337131823 |

### Datos técnicos

|                         |                           |
|-------------------------|---------------------------|
| Marco cobertor 1e:      | B 80,8 x H 80,8 x T 11,4  |
| Marco cobertor 2e:      | B 80,8 x H 151,9 x T 11,4 |
| Marco cobertor 2e s/LC: | B 80,8 x H 151,9 x T 11,4 |
| Marco cobertor 3e:      | B 80,8 x H 223,4 x T 11,4 |
| Marco cobertor 4e:      | B 80,8 x H 297,7 x T 11,4 |
| Marco cobertor 5e:      | B 80,8 x H 366,0 x T 11,4 |
| Radio de esquina:       | R 0,5                     |

