







Marco cobertor Gira F300 antracita (pintado)



Especificación	Ref.	UE	SP	EAN
 1 elemento	0211 83	1/10		4010337113461
 2 elementos	0212 83	1/10		4010337113515
 2 elementos sin listón central	1002 83	1/10		4010337131878
 3 elementos	0213 83	1/5		4010337113560
 4 elementos	0214 83	1/5		4010337113614
 5 elementos	0215 83	1/5		4010337131861

Características

- En el color blanco puro brillante: fabricado con un 85 % de plástico biocircular.

Datos técnicos

Marco cobertor 1e:	B 80,8 x H 80,8 x T 11,4
Marco cobertor 2e:	B 80,8 x H 151,9 x T 11,4
Marco cobertor 2e s/LC:	B 80,8 x H 151,9 x T 11,4

Marco cobertor 3e:	B 80,8 x H 223,4 x T 11,4
Marco cobertor 4e:	B 80,8 x H 297,7 x T 11,4
Marco cobertor 5e:	B 80,8 x H 366,0 x T 11,4
Radio de esquina:	R 0,5
Plastica biocircolare - Color: blanco brillante:	mín. 50 %
