

Marco cobertor Gira E2 color aluminio

| Especificación | Ref. | UE | SP | EAN |
|--|---------|----------|----|---------------|
|  1 elemento | 0211 25 | 1/10/100 | 11 | 4010337211259 |
| 1 elemento | 6211 25 | 1/10/100 | 11 | 4010337105374 |
|  1,5 elementos | 1001 25 | 1/10 | 11 | 4010337881346 |
|  2 elementos | 0212 25 | 1/10 | 11 | 4010337212256 |
| 2 elementos | 6212 25 | 1/10 | 11 | 4010337105381 |
|  2 elementos sin listón central | 1002 25 | 1/10 | 11 | 4010337002253 |
|  3 elementos | 0213 25 | 1/5 | 11 | 4010337213253 |
| 3 elementos | 6213 25 | 1/5 | 11 | 4010337105398 |
|  4 elementos | 0214 25 | 1/5 | 11 | 4010337214250 |

 5 elementos

0215 25

1/5

11

4010337215257

Características

- Plástico: termoplástico sin halógenos, resistente golpes y roturas o también policarbonato.

Notes

- También indicado para instalaciones en superficie.
- Marco cobertor (de 1 a 5 elementos) en combinación con el juego de juntas, también apropiado para la instalación empotrada IP44 protegida del agua.