










## Tecla basculante de 1 elemento sin imprimir con visor de control System 55



| Especificación   | Ref.     | UE  | SP | EAN           |
|--|----------|-----|----|---------------|
|  • blanco crema brillante | 5371 01  | 1/5 |    | 4010337108337 |
|  • blanco brillante     | 5371 03  | 1/5 |    | 4010337108344 |
|  • blanco mate          | 5371 27  | 1/5 |    | 4010337108351 |
|  • antracita            | 5371 28  | 1/5 |    | 4010337108368 |
|  • color aluminio       | 5371 26  | 1/5 |    | 4010337108375 |
|  • negro mate           | 5371 005 | 1/5 |    | 4010337108382 |
|  • gris mate            | 5371 015 | 1/5 |    | 4010337108399 |
|  • acero inoxidable     | 5371 600 | 1/5 |    | 4010337108405 |

## Características

- Tecla basculante de mando sin impresión como repuesto de las teclas basculantes originales identificadas con símbolos.

---

## Notes

- En caso de usarse un módulo de superficie de metal o un marco cobertor de metal, el alcance puede verse afectado.

---