

Cadre de finition Gira F300 blanc satiné (laqué)



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 82	1/10	12,60	11	4010337113485
 2x	0212 82	1/10	19,13	11	4010337113546
 2x sans nervure centrale	1002 82	1/10	19,13	11	4010337131854
 3x	0213 82	1/5	31,46	11	4010337113591
 4x	0214 82	1/5	51,10	11	4010337113645
 5x	0215 82	1/5	77,75	11	4010337131847

Caractéristiques techniques

Cadre de fin. 1x:	B 80,8 x H 80,8 x T 11,4
Cadre de fin. 2x:	B 80,8 x H 151,9 x T 11,4
Cadre de fin. 2x s/NC:	B 80,8 x H 151,9 x T 11,4
Cadre de fin. 3x:	B 80,8 x H 223,4 x T 11,4
Cadre de fin. 4x:	B 80,8 x H 297,7 x T 11,4
Cadre de fin. 5x:	B 80,8 x H 366,0 x T 11,4
Rayon d'angle:	R 0,5

