







## Cadre de finition Gira F100 anthracite (laqué)



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 173	1/10	12,60	11	4010337135951
 2x	0212 173	1/10	19,13	11	4010337133568
 2x sans nervure centrale	1002 173	1/10	19,13	11	4010337133605
 3x	0213 173	1/5	31,46	11	4010337133575
 4x	0214 173	1/5	51,10	11	4010337133582
 5x	0215 173	1/5	77,75	11	4010337133599

### Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

### Caractéristiques techniques

Cadre de fin. 1x:	B 83,3 x H 83,3 x T 10,6
Cadre de fin. 2x:	B 83,3 x H 154,4 x T 10,6
Cadre de fin. 2x s/NC:	B 83,3 x H 154,4 x T 10,6

Cadre de fin. 3x:	B 83,3 x H 225,9 x T 10,6
Cadre de fin. 4x:	B 83,3 x H 297,2 x T 10,6
Cadre de fin. 5x:	B 83,3 x H 368,5 x T 10,6
Rayon d'angle:	R 3
Plastique biocirculaire - Version: blanc brillant:	min. 50%

---