

## Cadre de finition Gira E2 pour le montage plat blanc satiné



| Spécification                                                                                                | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  1x                         | 0211 225 | 1/10 | 9,19           | 01 | 4010337021360 |
|  2x                       | 0212 225 | 1/10 | 14,77          | 01 | 4010337021377 |
|  2x sans nervure centrale | 1002 225 | 1/10 | 14,77          | 01 | 4010337021407 |
|  3x                       | 0213 225 | 1/5  | 24,34          | 01 | 4010337021384 |
|  4x                       | 0214 225 | 1/5  | 38,60          | 01 | 4010337021391 |

### Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.