

Cadre de finition Gira F100 blanc satiné (laqué)



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 172	1/10	12,60	11	4010337133506
 2x	0212 172	1/10	19,13	11	4010337133513
 2x sans nervure centrale	1002 172	1/10	19,13	11	4010337133551
 3x	0213 172	1/5	31,46	11	4010337133520
 4x	0214 172	1/5	51,10	11	4010337133537
 5x	0215 172	1/5	77,75	11	4010337133544

Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

Caractéristiques techniques

Cadre de fin. 1x:	B 83,3 x H 83,3 x T 10,6
Cadre de fin. 2x:	B 83,3 x H 154,4 x T 10,6
Cadre de fin. 2x s/NC:	B 83,3 x H 154,4 x T 10,6

Cadre de fin. 3x: B 83,3 x H 225,9 x T 10,6

Cadre de fin. 4x: B 83,3 x H 297,2 x T 10,6

Cadre de fin. 5x: B 83,3 x H 368,5 x T 10,6

Rayon d'angle: R 3

Plastique biocirculaire
- Version: blanc brillant: min. 50%
