

Cadre de finition Gira E2 anthracite

Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 23	1/10/100	8,16	11	4010337211235
 1,5x	1001 23	1/10	12,02	11	4010337881339
 2x	0212 23	1/10/100	11,79	11	4010337212232
 2x sans nervure centrale	1002 23	1/10	11,79	11	4010337002239
 3x	0213 23	1/5	20,42	11	4010337213239
 4x	0214 23	1/5	32,89	11	4010337214236
 5x	0215 23	1/5	50,15	11	4010337215233

Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.

Indications

- Convient également pour installations en goulotte.
 - En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.
-