

Cadre de finition Gira F200 blanc brillant



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 1x	0211 70	1/10	7,80	01	4010337113171
 2x	0212 70	1/10	13,77	01	4010337113225
 2x sans nervure centrale	1002 70	1/10	13,77	01	4010337113430
 3x	0213 70	1/5	22,23	01	4010337113270
 4x	0214 70	1/5	35,78	01	4010337113331
 5x	0215 70	1/5	54,65	01	4010337113386

Caractéristiques techniques

Cadre de fin. 1x:	B 90,0 x H 90,0 x T 11,4
Cadre de fin. 2x:	B 90,0 x H 161,1 x T 11,4
Cadre de fin. 2x s/NC:	B 90,0 x H 161,1 x T 11,4
Cadre de fin. 3x:	B 90,0 x H 232,6 x T 11,4
Cadre de fin. 4x:	B 90,0 x H 303,9 x T 11,4
Cadre de fin. 5x:	B 90,0 x H 375,2 x T 11,4
Rayon d'angle:	R 0,3

Plastique biocirculaire
- Version: blanc brillant:

min. 50%