







## Cadre de finition Gira E2



| Spécification  | Réf.    | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|---------|------|----------------|----|---------------|
|  1x                         | 0211 33 | 1/10 | 19,86          | 11 | 4010337019794 |
|  2x                       | 0212 33 | 1/10 | 30,78          | 11 | 4010337019800 |
|  2x sans nervure centrale | 1002 33 | 1/10 | 30,78          | 11 | 4010337019848 |
|  3x                       | 0213 33 | 1/5  | 56,58          | 11 | 4010337019817 |
|  4x                       | 0214 33 | 1/5  | 87,80          | 11 | 4010337019824 |
|  5x                       | 0215 33 | 1/5  | 133,72         | 11 | 4010337019831 |

### Indications

- Convient également pour installations en goulotte.
- En combinaison avec le kit d'étanchéité, le cadre de finition (1 à 5x) convient également pour le montage encastré protégé contre l'eau IP44.