

## Ancien - Bascule 2x



| Spécification                                                                                          | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  blanc crème brillant | 0295 01  | 1/10 | 0,00           |    | 4010337295013 |
|  blanc brillant     | 0295 03  | 1/10 | 0,00           |    | 4010337295037 |
|  blanc satiné       | 0295 27  | 1/10 | 0,00           |    | 4010337295273 |
|  anthracite         | 0295 28  | 1/10 | 0,00           |    | 4010337295280 |
|  teinte alu (laqué) | 0295 26  | 1/10 | 0,00           |    | 4010337295266 |
|  noir mat (laqué)   | 0295 005 | 1/10 | 0,00           |    | 4010337038078 |
|  gris mat (laqué)   | 0295 015 | 1/10 | 0,00           |    | 4010337080213 |
|  acier inoxydable   | 0295 600 | 1/10 | 0,00           |    | 4010337021728 |

## Caractéristiques

-

---