

## Cadre de finition Gira F100 blanc satiné (laqué)



| Spécification                                                                                                | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  1x                         | 0211 172 | 1/10 | 12,60          | 11 | 4010337133506 |
|  2x                       | 0212 172 | 1/10 | 19,13          | 11 | 4010337133513 |
|  2x sans nervure centrale | 1002 172 | 1/10 | 19,13          | 11 | 4010337133551 |
|  3x                       | 0213 172 | 1/5  | 31,46          | 11 | 4010337133520 |
|  4x                       | 0214 172 | 1/5  | 51,10          | 11 | 4010337133537 |
|  5x                       | 0215 172 | 1/5  | 77,75          | 11 | 4010337133544 |

### Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

### Caractéristiques techniques

|                        |                           |
|------------------------|---------------------------|
| Cadre de fin. 1x:      | B 83,3 x H 83,3 x T 10,6  |
| Cadre de fin. 2x:      | B 83,3 x H 154,4 x T 10,6 |
| Cadre de fin. 2x s/NC: | B 83,3 x H 154,4 x T 10,6 |

Cadre de fin. 3x: B 83,3 x H 225,9 x T 10,6

Cadre de fin. 4x: B 83,3 x H 297,2 x T 10,6

Cadre de fin. 5x: B 83,3 x H 368,5 x T 10,6

Rayon d'angle: R 3

Plastique biocirculaire  
- Version: blanc brillant: min. 50%

---