

## Cadre de finition Gira E2 pour le montage plat anthracite



| Spécification                                                                                                | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  1x                         | 0211 235 | 1/10 | 9,56           | 11 | 4010337021278 |
|  2x                       | 0212 235 | 1/10 | 15,46          | 11 | 4010337021285 |
|  2x sans nervure centrale | 1002 235 | 1/10 | 15,95          | 11 | 4010337021315 |
|  3x                       | 0213 235 | 1/5  | 25,29          | 11 | 4010337021292 |
|  4x                       | 0214 235 | 1/5  | 40,07          | 11 | 4010337021308 |

### Caractéristiques

- Plastique : thermoplastique sans halogène, résistant aux chocs, ou alors on parle de polycarbonate.