

## Cadre de finition Gira F300 blanc brillant



| Spécification                                                                                                | Réf.    | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------------|---------|------|----------------|----|---------------|
|  1x                         | 0211 80 | 1/10 | 7,77           | 01 | 4010337113478 |
|  2x                       | 0212 80 | 1/10 | 10,67          | 01 | 4010337113539 |
|  2x sans nervure centrale | 1002 80 | 1/10 | 10,67          | 01 | 4010337131830 |
|  3x                       | 0213 80 | 1/5  | 19,47          | 01 | 4010337113584 |
|  4x                       | 0214 80 | 1/5  | 31,45          | 01 | 4010337113638 |
|  5x                       | 0215 80 | 1/5  | 47,99          | 01 | 4010337131823 |

### Caractéristiques

- Dans la version blanc pur brillant : composé à 85 % de plastique bio-circulaire.

### Caractéristiques techniques

|                        |                           |
|------------------------|---------------------------|
| Cadre de fin. 1x:      | B 80,8 x H 80,8 x T 11,4  |
| Cadre de fin. 2x:      | B 80,8 x H 151,9 x T 11,4 |
| Cadre de fin. 2x s/NC: | B 80,8 x H 151,9 x T 11,4 |

Cadre de fin. 3x: B 80,8 x H 223,4 x T 11,4

Cadre de fin. 4x: B 80,8 x H 297,7 x T 11,4

Cadre de fin. 5x: B 80,8 x H 366,0 x T 11,4

Rayon d'angle: R 0,5

Plastique biocirculaire  
- Version: blanc brillant: min. 50%