










Cache avec cache rapporté pour module rapporté détecteur de mouvement 1,10 m Standard



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	1470 01	1	5,47	02	4010337020967
 blanc brillant	1470 03	1	5,47	02	4010337020974
 blanc satiné	1470 27	1	5,47	02	4010337075257
 anthracite	1470 28	1	9,06	02	4010337075264
 teinte alu	1470 26	1	14,54	02	4010337030010
 blanc brillant	1470 112	1	9,28	02	4010337075240
 teinte alu	1470 65	1	33,83	02	4010337075516
 blanc	1470 66	1	24,71	02	4010337075523
 anthracite	1470 67	1	33,83	02	4010337075530

