

## Interrupteur inverseur universel



| Spécification                                                                                          | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  blanc crème brillant | 2832 01  | -    | -              | -  | 4010337832010 |
|  blanc brillant     | 2832 03  | 1/10 | 36,52          | 29 | 4010337832034 |
|  anthracite         | 2832 28  | 1/10 | 39,25          | 29 | 4010337832287 |
|  teinte alu (laqué) | 2832 26  | 1/10 | 43,42          | 29 | 4010337832263 |
|  noir mat (laqué)   | 2832 005 | 1/10 | 43,42          | 11 | 4010337038528 |
|  gris mat (laqué)   | 2832 015 | 1/10 | 43,42          | 11 | 4010337087120 |

### Caractéristiques techniques

|                                                            |                    |
|------------------------------------------------------------|--------------------|
| Profondeur de montage:                                     | 25 mm              |
| section de raccordement<br>- Pour les conducteurs jusqu'à: | 2,5mm <sup>2</sup> |

## Indications

- Uniquement pour fixation par vis.

---