






Prise avec contact de mise à la terre EURO-US 16 A 250 V~



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2840 01	-	-	-	4010337840015
 blanc brillant	2840 03	-	-	-	4010337840039
 blanc satiné	2840 27	-	-	-	4010337840275
 anthracite	2840 28	-	-	-	4010337840282
 teinte alu	2840 26	-	-	-	4010337840268
noir mat	2840 005	-	-	-	4010337037873

Caractéristiques techniques

Profondeur de montage: 20 mm