

Bouton-poussoir à bascule 3x 10 A 250 V~ avec bascules Contact NO à 1 pôle



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	2844 01	1/10	38,42	29	4010337082033
 blanc brillant	2844 03	1/10	38,42	29	4010337082040
 anthracite	2844 28	1/10	41,20	29	4010337082064
 teinte alu	2844 26	1/10	45,30	29	4010337082057
 noir mat	2844 005	1/10	45,30	29	4010337037903
 gris mat	2844 015	1/10	45,30	29	4010337087182
 acier inoxydable (laqué)	2844 600	1/10	49,19	29	4010337021957

Caractéristiques techniques

Profondeur de montage: 25 mm

section de raccordement
- Pour les conducteurs jusqu'à: 2,5mm²

Indications

- Uniquement pour fixation par vis.
