










## Bascule avec symbole Sonnette



| Spécification  | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--|----------|------|----------------|----|---------------|
|  blanc crème brillant | 3286 01  | 1    | 6,05           | 01 | 4010337039723 |
|  blanc brillant     | 3286 03  | 1/10 | 6,05           | 01 | 4010337039730 |
|  blanc satiné       | 3286 27  | 1/10 | 6,05           | 01 | 4010337039754 |
|  anthracite         | 3286 28  | 1/10 | 6,58           | 11 | 4010337039761 |
|  teinte alu         | 3286 26  | 1    | 9,95           | 11 | 4010337039747 |
|  noir mat           | 3286 005 | 1/5  | 9,95           | 11 | 4010337067870 |
|  gris mat           | 3286 015 | 1    | 9,95           | 11 | 4010337110477 |
|  acier inoxydable   | 3286 600 | 1    | 17,56          | 11 | 4010337045151 |