









Bascule 2x avec symbole de flèche



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3294 01	1/10	11,25	01	4010337041191
 blanc brillant	3294 03	1/10/100	11,25	01	4010337041429
 blanc satiné	3294 27	1/10	11,25	01	4010337041443
 anthracite	3294 28	1/10	11,84	11	4010337041450
 teinte alu	3294 26	1/10	15,26	11	4010337041436
 noir mat	3294 005	1/10/100	15,73	11	4010337065746
 gris mat	3294 015	1/10	15,73	11	4010337110507
 acier inoxydable	3294 600	1/10	22,79	11	4010337045380