


## Bascule 2x avec symbole de flèche



| Spécification                                                                                          | Réf.     | UV.      | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|----------|----------------|----|---------------|
|  blanc crème brillant | 3294 01  | 1/10     | 11,25          | 01 | 4010337041191 |
|  blanc brillant     | 3294 03  | 1/10/100 | 11,25          | 01 | 4010337041429 |
|  blanc satiné       | 3294 27  | 1/10     | 11,25          | 01 | 4010337041443 |
|  anthracite         | 3294 28  | 1/10     | 11,84          | 11 | 4010337041450 |
|  teinte alu (laqué) | 3294 26  | 1/10     | 15,26          | 11 | 4010337041436 |
|  noir mat (laqué)   | 3294 005 | 1/10/100 | 15,73          | 11 | 4010337065746 |
|  gris mat (laqué)   | 3294 015 | 1/10     | 15,73          | 11 | 4010337110507 |
|  acier inoxydable   | 3294 600 | 1/10     | 22,79          | 11 | 4010337045380 |