









Bascule 2x



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3295 01	1/10	8,21	01	4010337040811
 blanc brillant	3295 03	1/10/100	8,21	01	4010337040828
 blanc satiné	3295 27	1/10	8,21	01	4010337040842
 anthracite	3295 28	1/10	8,81	11	4010337040859
 teinte alu	3295 26	1/10	12,23	11	4010337040835
 noir mat	3295 005	1/10	12,23	11	4010337065616
 gris mat	3295 015	1/10/100	12,23	11	4010337110514
 acier inoxydable	3295 600	1/5	19,74	11	4010337045267