









Bouton à bascule



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3296 01	1/10	4,32	21	4010337039341
 blanc brillant	3296 03	1/10/100	4,32	21	4010337039358
 blanc satiné	3296 27	1/10/100	4,32	21	4010337039372
 anthracite	3296 28	1/10/100	5,08	11	4010337039389
 teinte alu	3296 26	1/10	8,49	11	4010337039365
 noir mat	3296 005	1/10	8,49	11	4010337065593
 gris mat	3296 015	1/10	8,49	11	4010337110521
 acier inoxydable	3296 600	1/10	16,03	11	4010337043867