

## Bouton à bascule



| Spécification                                                                                          | Réf.     | UV.      | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|----------|----------------|----|---------------|
|  blanc crème brillant | 3296 01  | 1/10     | 4,32           | 21 | 4010337039341 |
|  blanc brillant     | 3296 03  | 1/10/100 | 4,32           | 21 | 4010337039358 |
|  blanc satiné       | 3296 27  | 1/10/100 | 4,32           | 21 | 4010337039372 |
|  anthracite         | 3296 28  | 1/10/100 | 5,08           | 11 | 4010337039389 |
|  teinte alu         | 3296 26  | 1/10     | 8,49           | 11 | 4010337039365 |
|  noir mat           | 3296 005 | 1/10     | 8,49           | 11 | 4010337065593 |
|  gris mat           | 3296 015 | 1/10     | 8,49           | 11 | 4010337110521 |
|  acier inoxydable   | 3296 600 | 1/10     | 16,03          | 11 | 4010337043867 |