


## Bascule 2x avec symboles de flèche



| Spécification                                                                                          | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  blanc crème brillant | 3297 01  | 1    | 11,25          | 01 | 4010337065821 |
|  blanc brillant     | 3297 03  | 1/10 | 11,25          | 01 | 4010337065838 |
|  blanc satiné       | 3297 27  | 1/10 | 11,25          | 01 | 4010337065869 |
|  anthracite         | 3297 28  | 1/10 | 11,84          | 11 | 4010337065890 |
|  teinte alu         | 3297 26  | 1    | 15,26          | 11 | 4010337065852 |
|  noir mat           | 3297 005 | 1/10 | 15,26          | 11 | 4010337065814 |
|  gris mat           | 3297 015 | 1    | 15,26          | 11 | 4010337110538 |