

## Bascule avec zone d'inscription



| Spécification                                                                                          | Réf.     | UV.  | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|------|----------------|----|---------------|
|  blanc crème brillant | 3299 01  | 1    | 8,54           | 01 | 4010337039471 |
|  blanc brillant     | 3299 03  | 1/10 | 8,54           | 01 | 4010337039488 |
|  blanc satiné       | 3299 27  | 1    | 8,54           | 01 | 4010337039501 |
|  anthracite         | 3299 28  | 1    | 9,08           | 11 | 4010337039518 |
|  teinte alu         | 3299 26  | 1    | 12,46          | 11 | 4010337039495 |
|  noir mat           | 3299 005 | 1    | 12,46          | 11 | 4010337066859 |
|  gris mat           | 3299 015 | 1    | 12,46          | 11 | 4010337110545 |
|  acier inoxydable   | 3299 600 | 1/5  | 20,04          | 11 | 4010337044956 |

## Etendue de la livraison

- Étiquette vierge fournie.
  - Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.
-