








Bascule 2x droite



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	3495 03	1	8,21	01	4010337065647
 blanc satiné	3495 27	1/10	8,21	01	4010337065661
 anthracite	3495 28	1	8,81	11	4010337065678
 teinte alu	3495 26	1	12,23	11	4010337065654
 noir mat	3495 005	1	12,23	11	4010337065630
 gris mat	3495 015	1	12,23	11	4010337110606
 acier inoxydable	3495 600	1/5	19,74	11	4010337065685