









## Bascule droite



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc brillant	3496 03	1/10	4,32	01	4010337121664
 blanc satiné	3496 27	1/10	4,32	01	4010337066101
 anthracite	3496 28	1/10	5,08	11	4010337066262
 teinte alu	3496 26	1	8,49	11	4010337065999
 noir mat	3496 005	1/10	8,49	11	4010337065944
 gris mat	3496 015	1	8,49	11	4010337110590
 acier inoxydable	3496 600	1/5	16,03	11	4010337066279