









## Bascule avec fenêtre de contrôle et zone d'inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	3670 01	1	9,95	01	4010337041740
 blanc brillant	3670 03	1	9,95	01	4010337041757
 blanc satiné	3670 27	1	9,95	01	4010337041771
 anthracite	3670 28	1	10,59	11	4010337041788
 teinte alu	3670 26	1	13,96	11	4010337041764
 noir mat	3670 005	1	13,96	11	4010337067078
 gris mat	3670 015	1	13,96	11	4010337110569

## Etendue de la livraison

- Les étiquettes avec les symboles « lumière », « sonnette » et « porte » sont fournies.