









Bascule avec symbole et zone d'inscription Sonnette



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|------|----------------|----|---------------|
|  blanc crème brillant | 3673 01 | 1 | 9,98 | 01 | 4010337039990 |
|  blanc brillant | 3673 03 | 1/10 | 9,98 | 01 | 4010337040040 |
|  blanc satiné | 3673 27 | 1/10 | 9,98 | 01 | 4010337040200 |
|  anthracite | 3673 28 | 1/5 | 10,60 | 11 | 4010337040217 |
|  teinte alu | 3673 26 | 1 | 13,98 | 11 | 4010337040057 |
|  noir mat | 3673 005 | 1 | 13,98 | 11 | 4010337067955 |
|  gris mat | 3673 015 | 1 | 13,98 | 11 | 4010337110576 |

Etendue de la livraison

- Étiquette vierge fournie.