










## Module rapporté de commande System 3000 System 55



| Spécification  | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5360 01  | 1/5 | 28,64          | 02 | 4010337027201 |
|  blanc brillant     | 5360 03  | 1/5 | 28,64          | 02 | 4010337027218 |
|  blanc satiné       | 5360 27  | 1/5 | 28,64          | 02 | 4010337027232 |
|  anthracite         | 5360 28  | 1/5 | 31,63          | 02 | 4010337027249 |
|  teinte alu         | 5360 26  | 1/5 | 36,36          | 02 | 4010337027225 |
|  noir mat           | 5360 005 | 1/5 | 36,36          | 02 | 4010337037453 |
|  gris mat           | 5360 015 | 1/5 | 36,36          | 02 | 4010337087205 |
|  acier inoxydable   | 5360 600 | 1/5 | 44,94          | 02 | 4010337027256 |

### Caractéristiques techniques

Température ambiante: -20 °C à +45 °C