









## Module rapporté de commande System 3000 symboles de flèche System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5361 01	1/5	32,95	02	4010337027270
 blanc brillant	5361 03	1/5	32,95	02	4010337027287
 blanc satiné	5361 27	1/5	32,95	02	4010337027300
 anthracite	5361 28	1/5	35,94	02	4010337027317
 teinte alu	5361 26	1/5	40,68	02	4010337027294
 noir mat	5361 005	1/5	40,68	02	4010337037477
 gris mat	5361 015	1/5	40,68	02	4010337087212
 acier inoxydable	5361 600	1/5	49,25	02	4010337027324

### Caractéristiques techniques

Température ambiante: -20 °C à +45 °C