


Bascule 2x sans impression avec fenêtre de contrôle System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5369 01	1/5	11,29	02	4010337460534
 blanc brillant	5369 03	1/5	11,29	02	4010337460589
 blanc satiné	5369 27	1/5	11,29	02	4010337063650
 anthracite	5369 28	1/5	14,27	02	4010337063643
 teinte alu (laqué)	5369 26	1/5	16,32	02	4010337063711
 noir mat (laqué)	5369 005	1/5	16,32	02	4010337063629
 gris mat (laqué)	5369 015	1/5	16,32	02	4010337087267
 acier inoxydable	5369 600	1/5	19,77	02	4010337063568

Caractéristiques

- Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
-

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-