

## Bascule 2x sans impression avec fenêtre de contrôle System 55



| Spécification                                                                                          | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5369 01  | 1/5 | 11,29          | 02 | 4010337460534 |
|  blanc brillant     | 5369 03  | 1/5 | 11,29          | 02 | 4010337460589 |
|  blanc satiné       | 5369 27  | 1/5 | 11,29          | 02 | 4010337063650 |
|  anthracite         | 5369 28  | 1/5 | 14,27          | 02 | 4010337063643 |
|  teinte alu (laqué) | 5369 26  | 1/5 | 16,32          | 02 | 4010337063711 |
|  noir mat (laqué)   | 5369 005 | 1/5 | 16,32          | 02 | 4010337063629 |
|  gris mat (laqué)   | 5369 015 | 1/5 | 16,32          | 02 | 4010337087267 |
|  acier inoxydable   | 5369 600 | 1/5 | 19,77          | 02 | 4010337063568 |

## Caractéristiques

- Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
- 

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-