

## Bascule 2x sans impression System 55



| Spécification                                                                                          | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5370 01  | 1/5 | 8,35           | 02 | 4010337108498 |
|  blanc brillant     | 5370 03  | 1/5 | 8,35           | 02 | 4010337108511 |
|  blanc satiné       | 5370 27  | 1/5 | 8,35           | 02 | 4010337108535 |
|  anthracite         | 5370 28  | 1/5 | 11,43          | 02 | 4010337108542 |
|  teinte alu (laqué) | 5370 26  | 1/5 | 13,48          | 02 | 4010337108528 |
|  noir mat (laqué)   | 5370 005 | 1/5 | 13,48          | 02 | 4010337108474 |
|  gris mat (laqué)   | 5370 015 | 1/5 | 13,48          | 02 | 4010337108481 |
|  acier inoxydable   | 5370 600 | 1/5 | 17,34          | 02 | 4010337108559 |

## Caractéristiques

- Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
- 

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-