


## Bascule 1x sans impression avec fenêtre de contrôle System 55



| Spécification                                                                                          | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5371 01  | 1/5 | 6,41           | 02 | 4010337108337 |
|  blanc brillant     | 5371 03  | 1/5 | 6,41           | 02 | 4010337108344 |
|  blanc satiné       | 5371 27  | 1/5 | 6,41           | 02 | 4010337108351 |
|  anthracite         | 5371 28  | 1/5 | 9,64           | 02 | 4010337108368 |
|  teinte alu (laqué) | 5371 26  | 1/5 | 11,56          | 02 | 4010337108375 |
|  noir mat (laqué)   | 5371 005 | 1/5 | 11,56          | 02 | 4010337108382 |
|  gris mat (laqué)   | 5371 015 | 1/5 | 11,56          | 02 | 4010337108399 |
|  acier inoxydable   | 5371 600 | 1/5 | 17,34          | 02 | 4010337108405 |

## Caractéristiques

- Bascule de commande sans inscription en remplacement de la bascule d'origine marquée de symboles.
- 

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-