

Bascule 2x avec symboles de flèche System 55



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 blanc crème brillant	5387 01	1/5	11,29	02	4010337111764
 blanc brillant	5387 03	1/5	11,29	02	4010337111771
 blanc satiné	5387 27	1/5	11,29	02	4010337111788
 anthracite	5387 28	1/5	14,27	02	4010337111795
 teinte alu (laqué)	5387 26	1/5	16,32	02	4010337111801
 noir mat (laqué)	5387 005	1/5	16,32	02	4010337111818
 gris mat (laqué)	5387 015	1/5	16,32	02	4010337111825
 acier inoxydable	5387 600	1/5	19,91	02	4010337111832

Caractéristiques

- Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
-

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-