

## Bascule 2x avec symboles de flèche System 55



| Spécification                                                                                          | Réf.     | UV. | EUR/pièce HTVA | SP | EAN           |
|--------------------------------------------------------------------------------------------------------|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5387 01  | 1/5 | 11,29          | 02 | 4010337111764 |
|  blanc brillant     | 5387 03  | 1/5 | 11,29          | 02 | 4010337111771 |
|  blanc satiné       | 5387 27  | 1/5 | 11,29          | 02 | 4010337111788 |
|  anthracite         | 5387 28  | 1/5 | 14,27          | 02 | 4010337111795 |
|  teinte alu         | 5387 26  | 1/5 | 16,32          | 02 | 4010337111801 |
|  noir mat           | 5387 005 | 1/5 | 16,32          | 02 | 4010337111818 |
|  gris mat           | 5387 015 | 1/5 | 16,32          | 02 | 4010337111825 |
|  acier inoxydable   | 5387 600 | 1/5 | 19,91          | 02 | 4010337111832 |

## Caractéristiques

- Toutes utilisables de manière universelle pour la bascule de gauche et de droite.
- 

## Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
-