










Bascule 1x avec symboles de flèche et fenêtre de contrôle System 55



| Spécification | Réf. | UV. | EUR/pièce HTVA | SP | EAN |
|--|----------|-----|----------------|----|---------------|
|  blanc crème brillant | 5388 01 | 1/5 | 7,71 | 02 | 4010337111856 |
|  blanc brillant | 5388 03 | 1/5 | 7,71 | 02 | 4010337111863 |
|  blanc satiné | 5388 27 | 1/5 | 7,71 | 02 | 4010337111870 |
|  anthracite | 5388 28 | 1/5 | 10,92 | 02 | 4010337111887 |
|  teinte alu | 5388 26 | 1/5 | 12,85 | 02 | 4010337111894 |
|  noir mat | 5388 005 | 1/5 | 12,85 | 02 | 4010337111900 |
|  gris mat | 5388 015 | 1/5 | 12,85 | 02 | 4010337111917 |
|  acier inoxydable | 5388 600 | 1/5 | 18,63 | 02 | 4010337111924 |

Caractéristiques

- Bascule de commande en remplacement de la bascule d'origine marquée de symboles.

Indications

- En cas d'utilisation d'un module rapporté en métal et/ou d'un cadre de finition en métal, la portée peut diminuer.
