







## Touche d appel System 106 avec zone d inscription



Spécification	Réf.	UV.	EUR/pièce HTVA	SP	EAN
 acier inoxydable	5547 920	1	41,58	20	4010337022770
 aluminium	5547 926	-	-	-	4010337022763
 blanc trafic (laqué)	5547 902	1	29,80	20	4010337022756
 acier inoxydable V4A	5547 914	1	56,30	20	4010337092063
 bronze	5547 921	1	56,30	20	4010337100935
 noir mat (laqué)	5547 925	1	56,30	20	4010337100775

### Caractéristiques techniques

Dimensions

- H x l:

25,3 x 105,5

### Indications

- Marquage professionnel via le service de marquage Gira [www.beschriftung.gira.de/fr/](http://www.beschriftung.gira.de/fr/).

---